



13237003

**Frame 2gang vert., K.5, al., al. anodised**

**Technical properties**

**Dimensions**

Depth	9.9 mm
Support plate thickness	max. 2 mm
Height	151.5 mm
Width	87 mm

**Capacity**

Number of sockets	2
-------------------	---

**Materials**

Colour of design line	Aluminium
Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	aluminium, anodised
Material	Aluminium
Surface appearance	matt
Type of surface treatment	Anodised

**Installation, mounting**

Installation mode	clamp fastening
-------------------	-----------------

**Safety**

Protection index IP	IP20
---------------------	------

**Identification**

Main design line	Berker K.5
------------------	------------

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---