



13237009

**Frame 2gang vert., K.1, p. white glossy**

**Technical properties**

**Dimensions**

Depth	9.9 mm
Support plate thickness	max. 2 mm
Height	151.5 mm
Width	87 mm

**Capacity**

Number of sockets	2
-------------------	---

**Materials**

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy
Type of surface treatment	untreated

**Installation, mounting**

Installation mode	clamp fastening
-------------------	-----------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Identification**

Main design line	Berker K.1
------------------	------------

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---