



13237009

Frame 2gang vert., K.1, p. white glossy

Technical properties

Dimensions

Depth	9.9 mm
Support plate thickness	max. 2 mm
Height	151.5 mm
Width	87 mm

Capacity

Number of sockets	2
-------------------	---

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	glossy
Type of surface treatment	untreated

Installation, mounting

Installation mode	clamp fastening
-------------------	-----------------

Safety

Protection index IP	IP20
---------------------	------

Identification

Main design line	Berker K.1
------------------	------------

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set.
-------------------	---