



1388

Glass cover plate 8gang facet , TS, clear glossy

Technical properties

Dimensions

Depth	5 mm
Screw length	25 mm
Height	160 mm
Width	86 mm

Materials

Colour of design line	clear
Surface appearance	glossy
Material / surface	with all-round facet

Installation, mounting

Screws / screwdriver	with screwdriver ; each with 2 M3.5 x 25 mm two-hole screws in chrome, gold and stainless steel for dismantling protection
Installation mode	for vertical and horizontal mounting ; clamp fastening

Equipment

Subplate	with polar white plastic base
----------	-------------------------------

Safety

Impact strength	IK02
-----------------	------

Identification

Main design line	Berker TS
------------------	-----------