



1394

Glass cover plate 4gang TS polar white glossy

Technical properties

Dimensions

Depth	5 mm
Screw length	25 mm
Height	160 mm
Width	86 mm

Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy
Material / surface	glass with polar white imprint on the rear

Installation, mounting

Screws / screwdriver	with screwdriver ; each with 2 M3.5 x 25 mm two-hole screws in chrome, gold and stainless steel for dismantling protection
Installation mode	for vertical and horizontal mounting ; clamp fastening

Equipment

Subplate	with polar white plastic base
----------	-------------------------------

Safety

Impact strength	IK02
-----------------	------

Identification

Main design line	Berker TS
------------------	-----------

Instructions

Information text	Other components from the B.7 glass range are available, e.g. SCHUKO socket outlets. Observe scale drawings!
------------------	--