



181112

Push-button, NO contact, TS, gold glossy, 24-carat galvanised

Technical properties

Architecture

Type of control unit Push button

Configuration

Switch mode Normally open contact

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 12 V

Rated voltage 12 V

Electric current

Momentary-contact current 1.5 A

Dimensions

Depth 19.7 mm

Insertion depth 13 mm

Height 22 mm

Width 22 mm

Materials

Colour of design line gold

Material / workmanship 24-carat galvanised

Surface appearance glossy

Material / surface brass, refined

Installation, mounting

Installation mode for screw fastening

Connection

Type of connection with plug-in terminals

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -20...60 °C

Identification

Main design line

Berker TS

Instructions

Special note text

For connection via system interfaces to radio bus, KNX radio or KNX installations. Alternatively, can be used to control relay circuits.