



18721030

### Wall box 3gang for hollow-wall mounting, R.8, light grey

#### Technical properties

##### Dimensions

|                    |       |
|--------------------|-------|
| Insertion depth    | 59 mm |
| Surface adjustment | 30 mm |

##### Materials

|                                    |           |
|------------------------------------|-----------|
| Colour independent of design lines | white     |
| Colour                             | white     |
| Colour                             | white     |
| Surface appearance                 | matt      |
| Type of surface treatment          | untreated |

##### Installation, mounting

|                   |  |
|-------------------|--|
| Installation mode | for flush-mounted and hollow-wall mounting ; with drilling template for hollow-wall mounting ; with installation material and mounting adaptor for each flush-mounted insert ; screw connection of each module insert via attached adapter with the wall box |
| Fixing of devices | screwing   |

##### Cable

|      |   |
|------|---|
| Wire | Cable entry possible from top, bottom and also from the side depending on the module insert |
|------|---|

##### Identification

|                  |            |
|------------------|------------|
| Main design line | Berker R.8 |
|------------------|------------|

##### Instructions

|                  |   |
|------------------|---|
| Information text | Fit the wall box in a flush Berker R.8 design line housing (order no. 1872 00 x0) for flush-mounted installation. |
|------------------|---|