



20342089

**Thermostat, NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,R.1.3**

**Technical properties**

**Functions**

Switching	with on/off switch and 2 LEDs
With cooling function	No

**Main electrical features**

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

**Electric current**

Switching current	16 (2) A
-------------------	----------

**Materials**

Colour of design line	polar white
-----------------------	-------------

**LED control**

LED	with LED for heating and LED for night lowering
-----	---

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Sensor cable length	4 m
Type of connection	with screw terminals
Connection	with separate connection for night lowering

**Settings**

Floor temperature setting range	10...50 °C
Room temperature setting range	5...30 °C

**Equipment**

Night lowering	≈ 5 K
Switching temperature difference	≈ 1 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

**Use**

Differentiation characteristic 1 - Sales	with rocker switch
Differentiation characteristic 3 - Sales	external temperature sensor

**Safety**

---

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

---

**Use conditions**

Energy efficiency class	I (1%)
-------------------------	--------

---

**Identification**

Application, usage	HVAC control
--------------------	--------------

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
--------------------------	--------------------------------------

---

**Instructions**

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--