



20347103

Thermostat, NO contact, Cen. plate, f. heat., rocker switch, ext. temp. sen., K5, al.

#### Technical properties

#### Functions

Switching with on/off switch and 2 LEDs

#### Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

#### Electric current

Switching current 10 A

#### Dimensions

Insertion depth 28.7 mm

#### Materials

Colour of design line	aluminium
Material / workmanship	lacquered

#### LED control

LED with LED for heating and LED for night lowering

#### Installation, mounting

Installation mode without spreader claws

#### Connection

Sensor cable length	4 m
Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

#### Settings

Floor temperature setting range	10...50 °C
Room temperature setting range	5...30 °C

#### Equipment

Night lowering	≈ 5 K
Switching temperature difference	≈ 1 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

#### Use

Differentiation characteristic 1 - Sales with rocker switch

**Use conditions**

---

Energy efficiency class	I (1%)
-------------------------	--------

**Identification**

---

Application, usage	HVAC control
--------------------	--------------

---

Main design line	Berker K.5
------------------	------------