



260009

## 230 V USB charging soc. out., com-tech, p. white, matt, plastic

### Technical properties

#### Connectivity

Connectors / jacks with 2 USB sockets type A

#### Main electrical features

Rated voltage 100...240 V

#### Voltage

Input voltage 100...240 V AC

Output voltage 5 V DC ( $\pm 5\%$ )

#### Electric current

Output current max. 1400 mA

Output current when operating both sockets max. 1.4 A

Output current per socket max. 1 A

#### Fuse

Fuse short-circuit and overload proof (electronic fuse)

#### Dimensions

Insertion depth 32 mm

#### Materials

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Surface appearance matt

#### Connection

Conductor cross-section (rigid) 2.5

USB connections according to DIN EN 50558

Type of connection with screw terminals (double for wiring through)

#### Use cases

Application Communication technology

#### Use

Differentiation characteristic 3 - Sales with screw terminals

#### Safety

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

**Identification**

Application, usage

Communication technology

Main design line

Modul-inserts

**Instructions**

Information text

No data transmission possible!