



26002045

## 230 V USB charging soc. out., 1930/R.classic, black glossy

### Technical properties

#### Connectivity

Connectors / jacks with 2 USB sockets type A

#### Main electrical features

Rated voltage 100...240 V

Rated current 1.4 A

#### Voltage

Input voltage 100...240 V AC

Output voltage 5 V DC

#### Electric current

Output current max. 1400 mA

Output current when operating both sockets max. 1.4 A

Output current per socket max. 1 A

#### Fuse

Fuse short-circuit and overload proof (electronic fuse)

#### Dimensions

Insertion depth 32 mm

#### Materials

Colour of design line black

#### Connection

USB connections according to DIN EN 50558

Type of connection with screw terminals (double for wiring through)

#### Equipment

Centre plates / central plates with centre plate Ø 58 mm

#### Use

Differentiation characteristic 3 - Sales with screw terminals

#### Safety

Protection without enhanced contact protection

#### Identification

Main design line Serie 1930/R.classic

#### Instructions

