



26002089

230 V USB charging soc. out., 1930/R.classic, p. white glossy

Technical properties

Connectivity

Connectors / jacks with 2 USB sockets type A

Main electrical features

Rated voltage 100...240 V

Rated current 1.4 A

Voltage

Input voltage 100...240 V AC

Output voltage 5 V DC

Electric current

Output current max. 1400 mA

Output current when operating both sockets max. 1.4 A

Output current per socket max. 1 A

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Insertion depth 32 mm

Materials

Colour of design line polar white

Connection

USB connections according to DIN EN 50558

Equipment

Centre plates / central plates with centre plate Ø 58 mm

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

Identification

Main design line Serie 1930/R.classic

