



296801

Speed cont., HVAC control

Technical properties

Electric current

Motor nominal and slat current max. 0.1...2.7 A

Fuse

Fine-wire fuse T 3.15 H 250 V

Fuse with spare fuse ; short-circuit and overload proof (fine-wire fuse)

Dimensions

Insertion depth 30.5 mm

Axis dimension \varnothing 4 mm

Power

Loss power at full load \approx 5 W

Connection

Type of connection with plug-in terminals

Contact additional switching contact for blade control

Settings

Setting basic speed adjustable

Equipment

Motor for devices with motory drive

Dimming principle phase cut-on

Switches / socket outlets with rotary on/off switch

Safety

REACH conform Yes

RoHS conform Yes

Identification

Application, usage HVAC control

Main design line HVAC-control

Instructions

Information text Possible to change fuse without removing cover.