



3031

Rocker switch off, Module inserts

Technical properties

Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

Configuration

Switch mode	Off
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	41.6 mm
Insertion depth	31 mm
Height	70.8 mm
Width	70.8 mm

Materials

Material	Plastic/metal
Surface appearance	other

Installation, mounting

Installation mode	with spreader claws, for screw fastening
-------------------	--

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals
Type of connection	Quickconnect

Equipment

Lighting	for lighting and monitoring circuit
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
Impact strength	IK07

Identification

Application, usage	Light control
Main design line	Light control
