



3031

Rocker switch off, Module inserts

Technical properties

Architecture

Type of control unit single rocker

Configuration

Switch mode Off

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 70.8 mm

Width 70.8 mm

Materials

Surface appearance other

Installation, mounting

Installation mode with spreader claws ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting for lighting and monitoring circuit

Heating switch	No
----------------	----

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Impact strength	IK07
-----------------	------

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Light control
------------------	---------------