



3032

## On/off switch 2pole 10 AX, light control

### Technical properties

#### Architecture

Type of control unit single rocker

#### Configuration

Switch mode 2-pole off ; with predefined neutral position

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Controls and indicators

Push-buttons No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

#### Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

#### Materials

Surface appearance matt

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

#### Equipment

Lighting for lighting and monitoring circuit

Heating switch No

**Use cases**

---

Application	Light control
-------------	---------------

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

**Identification**

---

Application, usage	Light control ; HVAC control
Appliance switch type	No
Main design line	Light control

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.
------------------	--