



3035

Series switch

Technical properties

Architecture

Type of control unit	double rocker
----------------------	---------------

Functions

Switching angle	3.5 °
-----------------	-------

Configuration

Switch mode	series
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	42 mm
Contact spacing	> 3 mm
Height	71 mm
Width	71 mm

Materials

Surface appearance	matt
--------------------	------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals
Type of connection	Quickconnect

Equipment	
Lighting	for lighting and monitoring circuit
Heating switch	No
Use cases	
Application	Light control
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
Identification	
Application, usage	Light control
Appliance switch type	No
Main design line	Light control
Instructions	
Information text	spreader claws, insulated to the supporting ring, self-resetting