


303520



Blind switch 1pole, blind control

Technical properties

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode with mechanical and electrical interlock to prevent mutual switch-on

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.5 mm

Height 70.8 mm

Width 70.8 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with plug-in terminals

Use cases

Application Blind control


Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Identification



Application, usage

Blind control

Main design line

Blind control