



303520

Blind switch 1pole, blind control

Technical properties

Architecture

Type of control unit	double rocker
Fixing mode	flush-mounting

Functions

Switching angle	3.5 °
-----------------	-------

Configuration

Switch mode	with mechanical and electrical interlock to prevent mutual switch-on
-------------	--

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	41.5 mm
Height	70.8 mm
Width	70.8 mm

Materials

Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Use cases

Application	Blind control
-------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Identification

Application, usage

Blind control

Main design line

Blind control