



3315396084

USB/3.5 mm audio socket outlet, Q.1/Q.3, aluminium velvety, lacquered

Technical properties

Connectivity

| | |
|--------------------|--|
| Outlet | with straight outlet |
| Connectors / jacks | USB, double socket type A, USB 2.0 compliant, double jack gold-plated 3.5 mm, stereo |

Dimensions

| | |
|-----------------|---------|
| Insertion depth | 24.9 mm |
|-----------------|---------|

Frequency

| | |
|-----------------------|----------------|
| Frequency range audio | 20 Hz...20 kHz |
|-----------------------|----------------|

Storage

| | |
|-----------------------|-----------------|
| USB transmission rate | max. 480 Mbit/s |
|-----------------------|-----------------|

Materials

| | |
|--------------------|----------------------------|
| Colour | aluminium |
| RAL colour | RAL 9006 - White aluminium |
| Material | Plastic/metal |
| Surface appearance | velvety |

Installation, mounting

| | |
|-------------------|------------------------|
| Installation mode | without spreader claws |
|-------------------|------------------------|

Identification

| | |
|--------------------------|--|
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |
|--------------------------|--|

Instructions

| | |
|------------------|---|
| Information text | Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 |
|------------------|---|