



3315397004

**USB/3.5 mm audio soc. out., K.5, stainless steel matt, lacq.**

**Technical properties**

**Connectivity**

Outlet	with straight outlet
Connectors / jacks	USB, double socket type A, USB 2.0 compliant ; double jack gold-plated 3.5 mm, stereo

**Dimensions**

Insertion depth	24.9 mm
-----------------	---------

**Frequency**

Frequency range audio	20 Hz...20 kHz
-----------------------	----------------

**Storage**

USB transmission rate	max. 480 Mbit/s
-----------------------	-----------------

**Materials**

Colour of design line	stainless steel
Material / workmanship	lacquered
Surface appearance	matt

**Installation, mounting**

Installation mode	without spreader claws ; for screw fastening
-------------------	--

**Identification**

Application, usage	Communication technology
Main design line	Berker K.5

**Instructions**

Information text	Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092
------------------	---