



3315397004

**USB/3.5 mm audio soc. out., K.5, stainless steel matt, lacq.**

**Technical properties**

**Connectivity**

|                    |  |
|--------------------|--|
| Outlet             | with straight outlet   |
| Connectors / jacks | USB, double socket type A, USB 2.0 compliant ;<br>double jack gold-plated 3.5 mm, stereo |

**Dimensions**

|                 |         |
|-----------------|---------|
| Insertion depth | 24.9 mm |
|-----------------|---------|

**Frequency**

|                       |                |
|-----------------------|----------------|
| Frequency range audio | 20 Hz...20 kHz |
|-----------------------|----------------|

**Storage**

|                       |                 |
|-----------------------|-----------------|
| USB transmission rate | max. 480 Mbit/s |
|-----------------------|-----------------|

**Materials**

|                        |                 |
|------------------------|-----------------|
| Colour of design line  | stainless steel |
| Material / workmanship | lacquered       |
| Surface appearance     | matt            |

**Installation, mounting**

|                   |  |
|-------------------|--|
| Installation mode | without spreader claws ; for screw fastening |
|-------------------|--|

**Identification**

|                    |                          |
|--------------------|--------------------------|
| Application, usage | Communication technology |
| Main design line   | Berker K.5               |

**Instructions**

|                  |   |
|------------------|---|
| Information text | Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 |
|------------------|---|