



3315397006

USB/3.5 mm audio soc. out., K.1, ant. matt, lacq.

Technical properties

Compatibility

Compatibility reverse-compatible to USB 2.0

Connectivity

Outlet with straight outlet

Connectors / jacks double jack gold-plated 3.5 mm, stereo ; USB, double socket type A, USB 3.0 compliant

Dimensions

Insertion depth 24.9 mm

Frequency

Frequency range audio 20 Hz...20 kHz

Storage

USB transmission rate max. 5 Gbit/s

Materials

Surface appearance matt

Installation, mounting

Installation mode without spreader claws

Safety

REACH conform Yes

RoHS conform Yes

Identification

Main design line Berker K.1

Instructions

Special note text New from September 2018! With USB 3.0 double jack.

Information text For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB). ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092