



3315407003

VGA soc. out., K.5, al., matt, lacq.

Technical properties

Connectivity

| | |
|--------------------|---|
| Outlet | with straight outlet |
| Plug type | S-VGA compatible |
| Connectors / jacks | with 15pole D-subminiature jack (front) |

Dimensions

| | |
|-----------------|-------|
| Insertion depth | 12 mm |
|-----------------|-------|

Frequency

| | |
|-----------------------|--------------|
| Frequency range video | max. 160 MHz |
|-----------------------|--------------|

Screen

| | |
|------------|---------------------|
| Resolution | max. 1280 x 1024 px |
|------------|---------------------|

Materials

| | |
|------------------------|-----------|
| Colour of design line | aluminium |
| Material / workmanship | lacquered |
| Surface appearance | matt |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | without spreader claws ; for screw fastening |
|-------------------|--|

Connection

| | |
|--------------------|---|
| Type of connection | with backside jack for connecting to pre-assembled VGA cable |
| Connection | with 15pole D-subminiature double jack |

Equipment

| | |
|------------------------------------|----------------------|
| Supporting plate / Supporting ring | with supporting ring |
|------------------------------------|----------------------|

Identification

| | |
|--------------------|--------------------------|
| Application, usage | Communication technology |
| Main design line | Berker K.5 |

Instructions

| | |
|------------------|--|
| Information text | For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 |
|------------------|--|