



3315422045

**High definition soc. out., R.1/R.3, black glossy**

**Technical properties**

**Architecture**

Number of poles 19pole

**Connectivity**

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

**Dimensions**

Insertion depth 16.8 mm

**Frequency**

Frequency range (vertical) 50...85 Hz

**Screen**

Resolution max. 1920 x 1080 px

**Storage**

Transmission rate max. 8.16 Gbit/s

**Materials**

Colour of labelling 217,217,217

Colour of design line black

Colour black

RAL colour RAL 9005 - Jet black

Material Plastic/metal

Material for printing PC-PMA black

Material / surface gold-plated contacts

**Installation, mounting**

Installation mode without spreader claws, for screw fastening

**Settings**

Shading parameter R1\_czarny

Laser parameter R1\_schwarz

**Equipment**

Type of configuration Laserdruck

**Safety**

REACH conform Yes

RoHS conform Yes

Identification	
Application, usage	Communication technology
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
Instructions	
	<p>Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ;</p> <p>Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ;</p> <p>Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092</p>
Information text	