



3315422089

High definition soc. out., R.1/R.3, p. white glossy

Technical properties

Architecture

Number of poles	19pole
-----------------	--------

Connectivity

Outlet	with straight outlet
Connectors / jacks	with HDMI double socket, type A, supports HDMI technology (V 2.1)

Dimensions

Insertion depth	16.8 mm
-----------------	---------

Frequency

Frequency range (vertical)	50...85 Hz
----------------------------	------------

Screen

Resolution	max. 1920 x 1080 px
------------	---------------------

Storage

Transmission rate	max. 8.16 Gbit/s
-------------------	------------------

Materials

Colour of design line	polar white
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal
Material for printing	ASA polar white
Material / surface	gold-plated contacts

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Settings

Shading parameter	R1_biały
Laser parameter	R1_weiß

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Safety

REACH conform	Yes
RoHS conform	Yes

Identification	
Application, usage	Communication technology
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
Instructions	
	<p>Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ;</p> <p>Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ;</p> <p>Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092</p>
Information text	