



3315426086

High definition soc. out., Q.x, ant. velvety, lacq.

#### Technical properties

##### Architecture

Number of poles 19pole

##### Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

##### Dimensions

Insertion depth 16.8 mm

##### Frequency

Frequency range (vertical) 50...85 Hz

##### Screen

Resolution max. 1920 x 1080 px

##### Storage

Transmission rate max. 8.16 Gbit/s

##### Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

Material / surface gold-plated contacts

##### Installation, mounting

Installation mode without spreader claws ; for screw fastening

##### Safety

REACH conform Yes

RoHS conform Yes

##### Identification

Application, usage Communication technology

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

##### Instructions

Information text

Installation recommendation: Kaiser: "Electronic box"  
for compliance with the permissible bending radii,  
Art. No. 1068-02 or 9062-74 ; For the connection of  
digital devices for transmission of high-resolution  
audio and video signals, such as satellite receivers  
and DVD players, to LCD or plasma screens. ;  
Observe the instructions of the cable and device  
manufacturers for maximum HDMI cable lengths! ;  
Fränkische: "Multimedia tube" for laying pre-  
assembled connection cable, Art. no. 294.10.092