



3315427003

**High definition soc. out., K.5, al., matt, lacq.**

#### Technical properties

##### Architecture

Number of poles 19pole

##### Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

##### Dimensions

Insertion depth 16.8 mm

##### Frequency

Frequency range (vertical) 50...85 Hz

##### Screen

Resolution max. 1920 x 1080 px

##### Storage

Transmission rate max. 8.16 Gbit/s

##### Materials

Colour aluminium

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance matt

Material / surface gold-plated contacts

##### Installation, mounting

Installation mode without spreader claws, for screw fastening

##### Identification

Application, usage Communication technology

Main design line Berker K.5

##### Instructions

Information text

Installation recommendation: Kaiser: "Electronic box"  
for compliance with the permissible bending radii,  
Art. No. 1068-02 or 9062-74 ; For the connection of  
digital devices for transmission of high-resolution  
audio and video signals, such as satellite receivers  
and DVD players, to LCD or plasma screens. ;  
Observe the instructions of the cable and device  
manufacturers for maximum HDMI cable lengths! ;  
Fränkische: "Multimedia tube" for laying pre-  
assembled connection cable, Art. no. 294.10.092