



3315427009

High definition soc. out., K.1, p. white glossy

Technical properties

Architecture

Number of poles 19pole

Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

Dimensions

Insertion depth 16.8 mm

Frequency

Frequency range (vertical) 50...85 Hz

Screen

Resolution max. 1920 x 1080 px

Storage

Transmission rate max. 8.16 Gbit/s

Materials

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Material / surface gold-plated contacts

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Safety

REACH conform Yes

RoHS conform Yes

Identification

Application, usage Communication technology

Main design line Berker K.1

Instructions

Information text

Installation recommendation: Kaiser: "Electronic box"
for compliance with the permissible bending radii,
Art. No. 1068-02 or 9062-74 ; For the connection of
digital devices for transmission of high-resolution
audio and video signals, such as satellite receivers
and DVD players, to LCD or plasma screens. ;
Observe the instructions of the cable and device
manufacturers for maximum HDMI cable lengths! ;
Fränkische: "Multimedia tube" for laying pre-
assembled connection cable, Art. no. 294.10.092