



3315431606

High definition soc. out. 90° plug connection, B.3/B.7, ant., matt

Technical properties

Architecture

Number of poles 19pole

Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

Dimensions

Insertion depth 41 mm

Frequency

Frequency range (vertical) 50...85 Hz

Screen

Resolution max. 1920 x 1080 px

Storage

Transmission rate max. 8.16 Gbit/s

Materials

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material Plastic/metal

Surface appearance matt

Material / surface gold-plated contacts

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Identification

Application, usage Communication technology

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Information text

Installation recommendation: Kaiser: "Electronic box"
for compliance with the permissible bending radii,
Art. No. 1068-02 or 9062-74 ; For the connection of
digital devices for transmission of high-resolution
audio and video signals, such as satellite receivers
and DVD players, to LCD or plasma screens. ;
Observe the instructions of the cable and device
manufacturers for maximum HDMI cable lengths! ;
Fränkische: "Multimedia tube" for laying pre-
assembled connection cable, Art. no. 294.10.092