



3315437009

**High definition soc. out. 90° plug connection, K.1, p. white glossy**

#### Technical properties

##### Architecture

Number of poles	19pole
-----------------	--------

##### Connectivity

Outlet	with straight outlet
--------	----------------------

Connectors / jacks	with HDMI double socket, type A, supports HDMI technology (V 2.1)
--------------------	---

##### Dimensions

Insertion depth	41 mm
-----------------	-------

##### Frequency

Frequency range (vertical)	50...85 Hz
----------------------------	------------

##### Screen

Resolution	max. 1920 x 1080 px
------------	---------------------

##### Storage

Transmission rate	max. 8.16 Gbit/s
-------------------	------------------

##### Materials

Colour of design line	polar white
-----------------------	-------------

Colour	polarwhite
--------	------------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	Plastic/metal
----------	---------------

Material / surface	gold-plated contacts
--------------------	----------------------

##### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

##### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

##### Identification

Application, usage	Communication technology
--------------------	--------------------------

Main design line	Berker K.1
------------------	------------

##### Instructions

Information text

Installation recommendation: Kaiser: "Electronic box"  
for compliance with the permissible bending radii,  
Art. No. 1068-02 or 9062-74 ; For the connection of  
digital devices for transmission of high-resolution  
audio and video signals, such as satellite receivers  
and DVD players, to LCD or plasma screens. ;  
Observe the instructions of the cable and device  
manufacturers for maximum HDMI cable lengths! ;  
Fränkische: "Multimedia tube" for laying pre-  
assembled connection cable, Art. no. 294.10.092