



383800

Group spring-return push-B 2p,isolated input term.,neut. poS,1930/glass/R.cl

Technical properties

Architecture

Type of control unit Short thumb-grip

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 42 mm

Insertion depth 32 mm

Height 71 mm

Width 42 mm

Installation, mounting

Installation mode with spreader claws

Use

Differentiation characteristic 3 - Sales with neutral-position

Safety

Protection index IP IP20

Identification

Main design line Serie 1930/Glas/R.classic

Secondary design line(s) Serie 1930 ; Serie 1930 Porzellan Made by Rosenthal ; Serie Glass ; Series R.classic

Instructions

Information text Without centre plate also suitable for mounting with glass and decor cover plates.