



383800

Group spring-return push-B 2p,isolated input term.,neut. poS,1930/glass/R.cl

Technical properties

Architecture

Type of control unit Short thumb-grip

Configuration

Switch mode with neutral position

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 42 mm

Insertion depth 32 mm

Height 71 mm

Width 42 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with neutral-position

Safety

Protection index IP IP20

Identification

Main design line Serie 1930/Glas/R.classic

Secondary design line(s) Serie 1930, Serie 1930 Porzellan Made by Rosenthal, Serie Glass, Series R.classic

Instructions

Information text Without centre plate also suitable for mounting with glass and decor cover plates.