



3861

### 3-step switches, neut. pos., HVAC control

#### Technical properties

##### Architecture

Type of control unit Rotative

##### Configuration

Switch mode with neutral position: 0-1-2-3

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 16 A

##### Electric current

Switching current 16 A

##### Dimensions

Depth 46 mm

Height 71 mm

Width 71 mm

##### Materials

Surface appearance other

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Type of connection with screw terminals

##### Use cases

Application HVAC-control

##### Use

Differentiation characteristic 3 - Sales with neutral-position

##### Identification

Application, usage HVAC control

Main design line HVAC-control

##### Instructions

Information text For air conditioners and fans, for example.