



3861

3-step switches, neut. pos., HVAC control

Technical properties

Architecture

Type of control unit	Rotative
Fixing mode	flush-mounting

Configuration

Switch mode	with neutral position: 0-1-2-3
-------------	--------------------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	16 A

Electric current

Switching current	16 A
-------------------	------

Dimensions

Depth	46 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
Surface appearance	other

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Use cases

Application	HVAC-control
-------------	--------------

Use

Differentiation characteristic 3 - Sales	with neutral-position
--	-----------------------

Safety

Protection index IP	IP20
---------------------	------

Identification

Application, usage	HVAC control
Main design line	HVAC-control

