



387700

Rot. switch, intermediate, 1930/glass/R.classic

Technical properties

Architecture

Type of control unit	Short thumb-grip
Fixing mode	flush-mounting

Configuration

Switch mode	intermediate
-------------	--------------

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	10 AX
-------------------	-------

Dimensions

Depth	42 mm
Height	71 mm
Width	71 mm

Materials

Material	duroplastic
----------	-------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without neon lamp
----------	-------------------

Safety

Protection index IP	IP20
---------------------	------

Identification

Appliance switch type	No
Main design line	Serie 1930/Glas/R.classic

