



387700

**Rot. switch, intermediate, 1930/glass/R.classic**

**Technical properties**

**Architecture**

Type of control unit	Short thumb-grip
Fixing mode	flush-mounting

**Configuration**

Switch mode	intermediate
-------------	--------------

**Controls and indicators**

Push-buttons	No
--------------	----

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC

**Electric current**

Switching current	10 AX
-------------------	-------

**Dimensions**

Depth	42 mm
Height	71 mm
Width	71 mm

**Materials**

Material	duroplastic
----------	-------------

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Type of connection	with screw terminals
Type of connection	Screw connection

**Equipment**

Lighting	without neon lamp
----------	-------------------

**Safety**

Protection index IP	IP20
---------------------	------

**Identification**

Appliance switch type	No
Main design line	Serie 1930/Glas/R.classic

