



387700

Rot. switch, intermediate, 1930/glass/R.classic

Technical properties

Architecture

Type of control unit Short thumb-grip

Configuration

Switch mode intermediate

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX

Dimensions

Depth 42 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting without neon lamp

Identification

Appliance switch type No

Main design line Serie 1930/Glas/R.classic

Secondary design line(s) Serie 1930 Porzellan Made by Rosenthal ; Serie 1930 ; Serie Palazzo ; Serie Glass