



395619

**Pullcord push-button, change-over contact sep. signal contact, light control**

**Technical properties**

**Architecture**

Type of control unit pull cord

**Configuration**

Switch mode change-over contact, with separate signal contact

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 10 A

**Dimensions**

Depth 42 mm

Insertion depth 31.2 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

**Length**

Long pullcord 14 cm

**Materials**

Surface appearance matt

**Installation, mounting**

Installation mode for wall and ceiling mounting ; with spreader claws

**Connection**

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

**Equipment**

Lighting for lighting and monitoring circuit

**Use cases**

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Identification**

---

Application, usage	Light control
Main design line	Light control

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--