



3966

Pullcord switch off/change-over 10 AX

Technical properties

Architecture

Type of control unit pull cord

Configuration

Switch mode Off/change-over

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 42 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

Length

Long pullcord 14 cm

Materials

Surface appearance matt

Installation, mounting

Installation mode for wall and ceiling mounting ; with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Plug-in connection

Equipment

Lighting	for lighting and monitoring circuit
Heating switch	No
Use cases	
Application	Light control
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Identification	
Application, usage	Light control
Appliance switch type	No
Main design line	Light control
Instructions	
Information text	spreader claws, insulated to the supporting ring, self-resetting