



3966

## Pullcord switch off/change-over 10 AX

### Technical properties

#### Architecture

Type of control unit	pull cord
Fixing mode	flush-mounting

#### Configuration

Switch mode	Off/change-over
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

#### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	42 mm
Contact spacing	> 3 mm
Height	71 mm
Width	71 mm

#### Length

Long pullcord	14 cm
---------------	-------

#### Materials

Material	Plastic/metal
Surface appearance	matt

#### Installation, mounting

Installation mode	for wall and ceiling mounting, with spreader claws
-------------------	--

#### Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals

Type of connection	Plug-in connection
<b>Equipment</b>	
Lighting	for lighting and monitoring circuit
Heating switch	No
<b>Use cases</b>	
Application	Light control
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Identification</b>	
Application, usage	Light control
Appliance switch type	No
Main design line	Light control
<b>Instructions</b>	
Information text	spreader claws, insulated to the supporting ring, self-resetting