



41431606

SCHUKO soc. out., screw-in lift terminals, B.3/B.7, ant., matt

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material	thermoplastic
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw terminals

Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP20
---------------------	------

Protection	without enhanced contact protection
------------	-------------------------------------

Identification

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
--------------------------	------------------------------------