



41432089

SCHUKO soc. out., screw-in lift terminals, R.1/R.3, p. white glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 105,105,105

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material for printing ASA polar white

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

Settings

Shading parameter R1_biały

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Protection	without enhanced contact protection
------------	-------------------------------------

With enhanced contact protection	No
----------------------------------	----

Identification

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
--------------------------	--------------------------------------