



41436084

SCHUKO socket outlet w. screw-in lift terminals, Q.x, alu velvety, lacquered

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

Metallic colour Yes

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

Use

Differentiation characteristic 3 - Sales with screw-in lift terminals

Safety

IK protection code against mechanical impacts 02

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No
Identification	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9