



41452045

SCHUKO soc.out.,mounting orient. var. in 45° steps,screw-in lift term.,R.cl,bl.

#### Technical properties

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

**Equipment**

Type of configuration

Laserdruck

**Use**

Differentiation characteristic 2 - Sales

Installation position variable in 45° steps

Differentiation characteristic 3 - Sales

with screw-in lift terminals

**Safety**

Protection index IP

IP20

Protection

without enhanced contact protection

With enhanced contact protection

No

**Identification**

Main design line

Serie R.classic