



41452045

SCHUKO soc.out., mounting orient. var. in 45° steps, screw-in lift term., R.cl, bl.

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 217,217,217

Colour of design line black

Colour black

Material for printing PC-PMA black

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

Equipment

Type of configuration Laserdruck

Use

Differentiation characteristic 2 - Sales	Installation position variable in 45° steps
Differentiation characteristic 3 - Sales	with screw-in lift terminals

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Serie R.classic
------------------	-----------------
