



4468

Cable out. low inst. depth, com-tech

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Relay space-saving for relays, etc.

Dimensions

Insertion depth 23.1 mm

Materials

Material Plastic/metal

Surface appearance other

Installation, mounting

Installation mode low installation depth, with spreader claws

Connection

Terminal without terminal block

Cable

Cable clamp with strain relief

Wire for lines Ø max. 9 mm

Use cases

Application Communication technology

Identification

Application, usage Communication technology

Main design line Accessories

Secondary design line(s) Communication technology, Serie Glass, Serie 1930

With imprint No