



4468

### Cable out. low inst. depth, com-tech

#### Technical properties

##### Functions

Relay space-saving for relays, etc.

##### Dimensions

Insertion depth 23.1 mm

##### Materials

Surface appearance other

##### Installation, mounting

Installation mode low installation depth ; with spreader claws

##### Connection

Terminal without terminal block

##### Cable

Cable clamp with strain relief

Wire for lines Ø max. 9 mm

##### Use cases

Application Communication technology

##### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

##### Identification

Application, usage Communication technology

Main design line Accessories

Secondary design line(s) Communication technology ; Serie Glass ; Serie 1930

With imprint No