



4468

## Cable out. low inst. depth, com-tech

### Technical properties

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

Relay	space-saving for relays, etc.
-------	-------------------------------

#### Dimensions

Insertion depth	23.1 mm
-----------------	---------

#### Materials

Material	Plastic/metal
Surface appearance	other

#### Installation, mounting

Installation mode	low installation depth, with spreader claws
-------------------	---

#### Connection

Terminal	without terminal block
----------	------------------------

#### Cable

Cable clamp	with strain relief
Wire	for lines Ø max. 9 mm

#### Use cases

Application	Communication technology
-------------	--------------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Identification

Application, usage	Communication technology
Main design line	Accessories
Secondary design line(s)	Communication technology, Serie Glass, Serie 1930
With imprint	No