



4502

## Technical properties

### Connectivity

Reception / transmission for terrestrial reception ; for digital and analogue transmission

### Frequency

Broadband technology 4...2400 MHz

### Resistance

Wave impedance 75  $\Omega$

### Attenuation

Tap loss at 2150 MHz 5 dB

Tap loss at 860 MHz 4 dB

### Connection

Type of connection with screw terminals

### Identification

Main design line Communication technology